










7	7	5	5	0	0	0	N	N
---	---	---	---	---	---	---	---	---

室内機





仕様表

ユ ニ ッ ト				室内ユニット		室外ユニット	
タ イ プ				壁掛型セパレート			
型 式				RAS-AJ40G		RAC-AJ40G	
電 源				(50/60Hz)			
				単相100V			
冷 房	定格	能力	kW	4.0 (0.5 ~ 4.3)			
		消費電力	W	1,450 (190 ~ 1,765)			
		運転電流	A	16.1			
		力率	%	90			
暖 房	定格	能力	kW	5.0 (0.6 ~ 6.3)			
		消費電力	W	1,450 (195 ~ 1,980)			
		運転電流	A	16.1 (最大 20.0)			
		力率	%	90			
	低温	能力	kW	4.6			
		消費電力	W	1,765			
始 動 電 流			A	16.1			
通年エネルギー消費効率		JISC9612:2013		4.9			
		JISC9612:2005 (区分)		4.9 (C)			
冷 凍 装 置	圧縮機出力		W	—		1,100	
	熱交換器フィン形状			細幅スリット		コルゲート	
	冷媒	種類		フロン R32			
封入量		g	950				
フ ア ン	種 類			貫流ファン		プロペラファン	
	ファンモータ出力		W	25		40	
	風 量 (冷房・暖房)	急 速	m ³ /h	680 ・ 780		1,860・1,740	
		強 風	m ³ /h	520 ・ 680		—	
		弱 風	m ³ /h	410 ・ 510		—	
		微 風	m ³ /h	340 ・ 400		—	
		静	m ³ /h	260 ・ 260		—	
音響パワーレベル 運転音 (冷房・暖房)	急 速	dB	64 ・ 64		61 ・ 62		
	強 風	dB	55 ・ 58		—		
	弱 風	dB	49 ・ 51		—		
	微 風	dB	45 ・ 46		—		
	静	dB	42 ・ 41		—		
操作スイッチ		型名	ワイヤレスリモコン RAR-6Z2				
電源プラグ	容 量		125V-20A				
	形 状		㊦		—		
電源コード長さ (左/右)			m	0.6/1.3		—	
室内外接続 ケーブル	芯線径 (φ)	mm	2.0				
	芯 数	芯	3				
冷媒配管	接続方式		フレア				
	液側 (φ)	mm	6.35				
	ガス側 (φ)	mm	9.52				
	最大配管長	m	20				
	最大高低差	m	10				
	冷媒追加充填量	g	チャージレス				
ドレン接続口外径 (φ)			mm	16			
外装色 (近似マンセルNo.)			クリアホワイト (N9.5)		ナチュラルグレー (2.9Y7.8/1)		
製品寸法 (高さ×幅×奥行)			mm	280×780×210		629×799(+99)×299(+68)	
荷造寸法 (幅×奥行×高さ)			cm	82×33×26		93×40×67	
質量 (製品・荷造)			kg	8.5 ・ 10.0		37.0 ・ 39.0	

注記








1. 室内機のサービススペースは左・右・上が 50 mm 必要です。カーテンレール、カーテンボックス等の上に設置する場合は、風の流れを損なわない寸法を確保してください。
2. 配管は太径、細径とも断熱してあるものを使用します。
3. 配管は長さ 2.0 m 以内です。
4. 室内・室外機の配管落差は 1.0 m 以内です。
5. プラグの形状 
6. 電源コードの長さ



SIGNATURE		DATE	PROJECTION	SCALE	TITLE			
DWN.	T. Endo	2017-03-07		N T S	RAS-AJ40G:RAC-AJ40G 構造・寸法図			
CHKD.	K. Odate	2017-03-09			Hitachi-Johnson Controls Air Conditioning, Inc.			TOCHIGI DWG. No.
APPD.	Y. Yasunaga	2017-03-09						3YAA NN0005577

8	7	5	5	0	0	0	N	N
---	---	---	---	---	---	---	---	---

室 外 機



注記

1. 本体の前、後、左、右、上方向に上図の $\longleftrightarrow$ 印の間隔をあけられ、
2 方向以上開放できるところに据え付けてください。
2. 効率のよい運転のため、周囲のスペースをできるだけ広くあけてください。


SIGNATURE		DATE	PROJECTION	SCALE	TITLE	
DWN.	M. Oguri	2017-03-09		N T S	RAS-AJ40G:RAC-AJ40G 構造:寸法図	
CHKD.	T. Fukuda	2017-03-17				
APPD.	Y. Yasunaga	2017-03-21				
			Hitachi-Johnson Controls Air Conditioning, Inc.		TOCHIGI DWG. No. 3YAA NN0005578	

This drawing is under license by Johnson Controls-Hitachi Air Conditioning Technology (Hong Kong) Limited



REGD.
REGD
2017
321

001



SIGNATURE	DATE	PROJECTION	SCALE	TITLE
DWN. M. Oguri	2017-03-16		NTS	RAS-AJ40G:RAC-AJ40G 回路図:配線図
CHKD. H. Shono	2017-03-21			
APPD. Y. Yasunaga	2017-03-21			
Hitachi-Johnson Controls Air Conditioning, Inc.				TOCHIGI DWG. No. 3YDANN0005579