

186015681

A

室内機

B

C

D

E

F

室内機サービススペース

Technical drawing of a window unit showing dimensions and installation details. The drawing includes a side view of the window unit with a width dimension of 100 and a height dimension of 100. The unit is shown installed in a wall, with a cross-section view indicating the internal structure and the placement of the window frame. The drawing is labeled with '100' and '100' at the top, indicating the dimensions of the unit.

7.2
イニシャル位置

7.2
イニシャル位置

5.0

8.0

仕様表

項目			形式	室内機		室外機	
				RAS-SC36Y		RAC-SC36Y	
電源 (50/60Hz)				単相100V			
冷凍装置	圧縮機出力 (W)			-		800	
	熱交換器フィン形状			細幅スリット		コルゲート	
	冷媒制御装置			-		電動膨張弁	
	冷媒切換装置			-		四方弁	
	冷媒	種類		フロン R410A			
		封入量 (g)		1,190 g			
	過負荷保護装置			自動復帰形			
	配管	配管接続方式		フレア			
パイプ径		細径	φ6.35				
	(外径φmm)	太径	φ9.52				
	ファンモータ出力 (W)			25		40	
送風装置	ファン (冷房・暖房)	種類		貫流ファン		プロペラファン	
		風量	強風	660・730		1,710・1,650	
		(m³/h)	弱風	530・610		-	
			微風	485・540		-	
電気特性	運転電流 (A)	冷房		9.0			
		暖房	ヒータ ON	-			
			ヒータ OFF	8.7 (最大 20.0)			
	消費電力 (W)	冷房		855 (70 ~ 1,210)			
		暖房	ヒータ ON	-			
			ヒータ OFF	825 (65 ~ 1,995)			
	力率 (%)	冷房		95			
		暖房	ヒータ ON	-			
			ヒータ OFF	95			
	始動電流 (A)	冷房		9.0			
暖房		8.7					
接続ケーブルの本数			3				
	電源プラグ	容量 (V-A)	125V-20A				
		形状	㊤		-		
冷房特性	冷房能力 (kW)			3.6 (0.5~4.1)			
	除湿能力 (ℓ/h)			1.9			
	冷房のめやす			10~15畳 (16~25m²)			
暖房特性	暖房能力 (kW)	ヒータON		-			
		ヒータOFF		4.2 (0.5~7.6)			
	電気ヒーター (W)		-				
	暖房のめやす		9~12畳 (15~19m²)				
機能	据付方式		背面引掛		-		
	主操作スイッチ		プッシュボタン (ワイヤレス) RAR-3Y1				
	表示ランプ		運転、タイマー、みはり、クリーン、ミスト、センサー				
風速切換			自動、強風、弱風、微風、静				
色調 (近似マンセルNO.)				ピュアホワイト (N9.5) シャインベージュ (10YR7/2)		Tベージュ (5Y7/2)	
外形寸法 (mm)		高さ	295		570		
		幅	798		750 (+86)		
		奥行	243		288 (+56)		
製品質量 (kg)		12		36			
騒音 (dB) (冷房・暖房)	強風		46・47		46・46		
	弱風		34・35		-		
	微風		28・30		-		
	静		21・22		-		
ドレン接続口 (外径φmm)				16			
付属品				壁掛据付部品一式			
電源コード長さ (m)		左/右	0.6/1.3		-		

- 本仕様は予告なく変更することがあります。

注記

1. 室内機のサービススペースは上記寸法が必要です。
カーテンレール、カーテンボックス等の上に設置する場合は、風の流れを損なわない寸法を確保してください。
2. 配管は太径、細径とも断熱してあるものを使用します。
3. 配管は長さ2.0m以内です。
4. 室内・室外機の配管落差は1.0m以内です。
5. プラグの形状 (㊹)
6. 電源コードの長さ

7. 接続ケーブルは、 $\phi 2.0 \times 3$ の単線 F ケーブルを使用します。

据 付 板 天井面（回縁）（ユニットを引っ掛けるために必要な寸法です。）




配管引出し穴中心線 (φ 65)

細径配管

本体中心線

ドレンホース



SIGNATURE		DATE		 	SCALE	TITLE	
DWN.	Y. Iizuka	2008-11-03	NTS		RAS-SC36Y:RAC-SC36Y 構造・寸法図		
CHKD.	T. Nagata	2008-11-04	Hitachi Appliances, Inc. Tokyo Japan		TOCHIGI DWG. No.		
APPD.	T. Nagata	2008-11-06					3YAA BB0015681

1

2

3

6

7

A

B

C

D

E

F

