








7008000NN


室内機





壁とのスペースは（ ）内の寸法をできるだけ確保してください。



ワイヤレスリモコン




リモコンホルダー



※横引き配管を行う時はドレンホースとドレンキャップを交換してください。


据 付 板 (正面图)

天井面（回縁）〔ユニットを引っ掛けるため
必要な寸法です。〕



注記

1. 室内機のサービススペースは左・右が50mm、
上が50mm、下が100mm必要です。
カーテンレール、カーテンボックス等の上に設置する
場合は、風の流れを損なわない寸法を確保してください。
2. 配管は太径、細径とも断熱してあるものを使用します。
3. 配管は長さ20m以内です。
4. 室内・室外機の配管落差は10m以内です。
5. プラグの形状 
6. 電源コードの長さ




7. 接続ケーブルは、 $\phi 2.0 \times 3$ の単線 F ケーブルを使用します。


仕様表

ユニットタイプ				室内ユニット		室外ユニット	
型式電源 (50/60Hz)				壁掛型セパレート		RAS-X63H2	
				RAC-X63H2			
能力 kW				6.3 (0.6 ~ 6.7)			
消費電力 W				1,760 (175 ~ 3,050)			
運転電流 A				10.1			
力率 %				87			
能力 kW				7.1 (0.6 ~ 11.7)			
消費電力 W				1,700 (145 ~ 3,900)			
運転電流 A				9.8 (最大 20.0)			
力率 %				87			
能力 kW				8.6			
消費電力 W				3,500			
始動電流 A				10.1			
通年エネルギー JISC9612:2013				6.7			
消費効率 JISC9612:2005 (区分)				6.6 (F)			
圧縮機出力 W				-		1,700	
熱交換器フィン形状				片起し3本スリット		コルゲート	
種類				フロン R32			
封入量 g				1,670			
種類				貫流ファン		プロペラファン	
ファンモータ出力 W				25		45	
風量				急速 m³/h		1,170・1,380	
(冷房・暖房)				強風 m³/h		990・1,120	
				弱風 m³/h		780・830	
				微風 m³/h		630・630	
				静 m³/h		420・450	
音響パワーレベル				急速 dB		66・70	
運転音				強風 dB		61・62	
(冷房・暖房)				弱風 dB		56・56	
				微風 dB		51・52	
				静 dB		37・38	
操作スイッチ 型式				ワイヤレスリモコン RAR-8C1			
電源プラグ				250V-20A			
電源コード長さ (左/右) m				0.6/1.3		-	
室内外接続ケーブル				芯線径 (φ) mm			
				芯数 芯			
				接続方式			
				液側 (φ) mm			
				ガス側 (φ) mm			
				最大配管長 m			
				最大高低差 m			
				冷媒追加充填量 g			
ドレン接続口外径 (φ) mm				16			
外装色 (近似マンセルNo.)				スターホワイト (N9.3)		ナチュラルグレー (2.9Y7.8/1)	
製品寸法 (高さ×幅×奥行) mm				295×798×374		709×859 (+97)×319 (+68)	
荷造寸法 (幅×奥行×高さ) cm				86×36×47		99×42×75	
質量 (製品・荷造) kg				17.0・20.0		43.0・45.0	

- (1) 本仕様は予告なく変更することがあります。
- (2) 定格冷房時の表示は、JIS条件(室内 27℃:DB・19℃:WB、室外 35℃:DB・24℃:WB)で運転した場合の数値です。
- (3) 定格暖房時の表示は、JIS条件(室内 20℃:DB・15℃:WB、室外 7℃:DB・6℃:WB)で運転した場合の数値です。
- (4) 低温暖房時の表示は、JIS条件(室内 20℃:DB・15℃:WB、室外 2℃:DB・1℃:WB)で運転した場合の数値です。
- (5) 能力、消費電力の()内の表示は、それぞれの可変幅(最小～最大)の数値です。
- (6) 運転音の表示は、JIS C 9612に基づき、無響室で測定した数値です。
- (7) 室外ユニットの製品寸法中()内の寸法について、幅方向はトッテとサービスバルブカバーの突き出し寸法を、また、奥行方向は空気吐出口と固定足の突き出し寸法を示しています。

SIGNATURE		DATE	PROJECTION	SCALE	TITLE			
DWN.	K. Daigou	2017-10-25		N T S	RAS-X63H2:RAC-X63H2 構造・寸法図			
CHKD.	K. Yoshida	2017-10-26	Hitachi-Johnson Controls Air Conditioning, Inc.			TOCHIGI DWG. No.		REGD. REGD
APPD.	K. Yoshida	2017-10-26				3YAA NN0008004		2017 1026





The diagram illustrates the electrical connections for a car stereo system. Key components and their connections include:

- Power Source:** A power plug (電源プラグ) with 50V/60Hz is connected to the power base (電源基板).
- Power Base (電源基板):** Divided into a relay side (リレー側) and a voltage side (電圧側). It includes a fuse (FU1 3A-FUSE), a relay (C123 R), and a transformer (TH001).
- Amplifier and Tuner:** The voltage side of the power base connects to an amplifier (V1) and a tuner (C1003). The amplifier output goes to a speaker (スピーカー).
- Wireless Remote (ワイヤレスリモコン):** Connected to the tuner section.
- Antenna (アンテナ):** Connected to the tuner section.
- Speakers (スピーカー):** The system includes a main speaker (スピーカー) and a sub-speaker (サブスピーカー).
- Wiring Details:** The diagram shows various wires (e.g., 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 45, 46, 47, 48, 49, 50, 51, 52, 53, 54, 55, 56, 57, 58, 59, 60, 61, 62, 63, 64, 65, 66, 67, 68, 69, 70, 71, 72, 73, 74, 75, 76, 77, 78, 79, 80, 81, 82, 83, 84, 85, 86, 87, 88, 89, 90, 91, 92, 93, 94, 95, 96, 97, 98, 99, 100) and their connections to various components.



- ※1 HA接続コード: 部品番号 [SP-HAC1]
- ※2 標準アダプター: HA-S100TSA
- ※3 RACアダプター: PSC-6RAD
- ※4 無線LAN接続アダプター: SP-WL2
- ※5 HEMSアダプター: SP-EM1

