







BB0040873

回路図

室内機

室外機

電源プラグ
単相100V
50/60Hz

ニ方弁コイル

室内ファン
モーター

VA001
(100V用)
R002
C001

TH001

NF1

DB1

T301

C342

R341

C343

C341

R342

C344

R343

C345

R344

C346

R347

C348

R349

C350

R351

C352

R353

C354

R355

C356

R357

C358

R359

C360

R361

C362

R363

C364

R365

RL001 (パワーリレー)

FU1 (3Aヒューズ)

C005

R003

C004

R004

C005

R006

C007

R008

C009

R010

C011

R012

C013

R014

C015

R016

C017

R018

C019

R020

C021

R022

C023

R024

C025

R026

C027

R028

C029

R030

C031

R032

C033

R034

C035

R036

C037

R038

F1 (25Aヒューズ)

VS1

CT1

L801

C801

R801

C802

R803

C804

R805

C806

R807

C808

R809

C810

R811

C812

R813

C814

R815

C816

R817

C818

R819

C820

R821

C822

R823

C824

R825

C826

R827

C828

R829

C830

R831

C832

R833

C834

R835

リフクタ 5.3mH

RL3 (全線/高電圧リレー)

F2 (10Aヒューズ)

DB601

Q601

C601

R601

C602

R603

C604

R605

C606

R607

C608

R609

C610

R611

C612

R613

C614

R615

C616

R617

C618

R619

C620

R621

C622

R623

C624

R625

C626

R627

C628

R629

C630

R631

C632

R633

C634

リフクタ 5.3mH

RL3 (全線/高電圧リレー)

F2 (10Aヒューズ)

DB601

Q601

C601

R601

C602

R603

C604

R605

C606

R607

C608

R609

C610

R611

C612

R613

C614

R615

C616

R617

C618

R619

C620

R621

C622

R623

C624

R625

C626

R627

C628

R629

C630

R631

C632

R633

C634

リフクタ 5.3mH

RL3 (全線/高電圧リレー)

F2 (10Aヒューズ)

DB601

Q601

C601

R601

C602

R603

C604

R605

C606

R607

C608

R609

C610

R611

C612

R613

C614

R615

C616

R617

C618

R619

C620

R621

C622

R623

C624

R625

C626

R627

C628

R629

C630

R631

C632

R633

C634

リフクタ 5.3mH

RL3 (全線/高電圧リレー)

F2 (10Aヒューズ)

DB601

Q601

C601

R601

C602

R603

C604

R605

C606

R607

C608

R609

C610

R611

C612

R613

C614

R615

C616

R617

C618

R619

C620

R621

C622

R623

C624

R625

C626

R627

C628

R629

C630

R631

C632

R633

C634

リフクタ 5.3mH

RL3 (全線/高電圧リレー)

F2 (10Aヒューズ)

DB601

Q601

C601

R601

C602

R603

C604

R605

C606

R607

C608

R609

C610

R611

C612

R613

C614

R615

C616

R617

C618